

Ultrane 548

DESCRIPTION AND GENERAL PROPERTIES

- **Material** Polyurethane foam
- **Length (inches)** 8.66-10.02 (depending on size)
- **Wrist** Knitted wrist
- **Colour/Color** Black
- **Interior finish** Seamless textile support
- **Exterior finish** Ventilated back
- **Size / EAN** 6 7 8 9 10 11
- **Packaging** 1 pair/bag - 12 pairs/bag - 96 pairs/carton
- **Complementary information** Guaranteed without silicone
Contains traces of DMF in compliance with occupational exposure limits



PERFORMANCE RESULTS

Certification category 2



3131

Legends



MECHANICAL HAZARDS
EN 388

PERFORMANCE LEVELS

0-4 0-5 0-4 0-4
 └─ Abrasion resistance
 └─ Blade cut resistance
 └─ Tear resistance
 └─ Puncture resistance



LOW CHEMICAL PROTECTION
EN 374



MICRO-ORGANISMS
EN 374



RADIOACTIVE CONTAMINATION
EN 421



HEAT AND FIRE
EN 407

PERFORMANCE LEVELS

0-4 0-4 0-4 0-4 0-4 0-4
 └─ Burning behaviour
 └─ Contact heat resistance
 └─ Convective heat resistance
 └─ Radiant heat resistant
 └─ Resistance to small drops of molten metal
 └─ Resistance to large quantities of molten metal



SPECIFIC CHEMICAL PROTECTION
EN 374

Letter Code	Chemical product
A	Methanol
B	Acetone
C	Acetonitrile
D	Dichloromethane
E	Carbon Disulfide
F	Toluene
G	Diethylamine
H	Tetrahydrofurane
I	Ethyl acetate
J	n-Heptane
K	Sodium hydroxide 40%
L	Sulphuric acid 96%



COLD HAZARDS
EN 511

PERFORMANCE LEVELS

0-4 0-4 0 or 1
 └─ Convective cold resistance
 └─ Contact cold resistance
 └─ Water permeability

For more details: www.mapa-pro.com

MAPA
PROFESSIONAL
www.mapa-pro.com

Ultrane 548

DESCRIPTION AND GENERAL PROPERTIES

- Thin glove: excellent tactile sensitivity
- Absorption of perspiration ensured by the cellular structure of the polyurethane. In addition, the particularly open texture of the specific lining helps improve hand ventilation
- Anatomical shape: close fit for precision

MAIN FIELDS OF USE

Automotive/mechanical industry

- Intricate assembly
- Sorting small parts
- Fitting small screws and fasteners

Electronics

- Assembly of electrical components
- Microprocessor handling

Cosmetics and Pharmaceutical industry

- Cosmetics preparation
- Medicine manufacturing

INSTRUCTIONS FOR USE

Instructions for use

- It is recommended to check that the gloves are suitable for the intended use, because the conditions of use in the workplace may differ from the tests performed in the laboratory.
- It is not recommended for persons sensitised to natural latex(glove with elastic wrist).
- Put the gloves on dry, clean hands.
- Ensure the inside of the gloves is dry before putting them on again.

Storage conditions

Store the gloves in their original packaging protected from heat, light and humidity.

Laundering conditions

Caution : using the gloves or submitting them to a cleaning or laundering process that is not specifically recommended can alter their performance levels.

LEGISLATION

This product is not classified as hazardous according to the directive 1999/45/EC of the European Parliament and of the Council.

This product does not contain more than 0.1% of substance of very high concern (SVHC) or any substance included in the annex XVII of regulation N°1097/2006 of the European parliament and of the Council (REACH)

- CE-Type Examination Certificate

0075/014/162/02/14/0117

- Issued by the notified body nr

0075

C.T.C.– 4 rue Herman FRENKEL - F-69367 LYON CEDEX 07